



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**XB6EAD222P**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

Degree of Protection: IP 65  
 Storage Temperature Range: -40 to +70 °C  
 Operating Temperature Range: -10 to +55 °C  
 Contact Type: 2 C/O  
 AC Supply Utilization Category: AC12, 120V-1.5A; 240V-1A; AC13, 120V-1A; 240V-0.7A  
 Certifications: IEC 60947-1, IEC 60947-5-1, JIS C 4520, JIS C 852, UL 508, CSA C22.2 No 14

Specification:

Description: Selector Switch, Round, black, 2 maintained positions, 2 NO/NC  
 Vibration Resistance: 1 mm (10...55 Hz)  
 Mechanical Shock Resistance: 10 gn (duration = 11 ms) for half sine wave acceleration  
 Mechanical Life (in operating cycles): 250000