



Note:  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**XPSABV11330C**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

Technical Information:

UL File/CCN: E164353 / NKCR  
 CSA File/Class: LR44087 / 3211 03  
 CE: Yes  
 RoHS: Yes

Description:  
 Voltage: 24 VDC  
 Terminal Type: Spring  
 Terminal Block: Removable  
 Safety Contacts - Standard: 2  
 Safety Contacts - Time Delay: 1  
 Auxiliary Contacts:  
 Solid State Outputs:  
 Timing Range: 1.5 - 30 s

Specification: