



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XSAV01801



Telemecanique
Sensors

Telemecanique Sensors
1875 Founders Drive
Dayton, OH 45420-4017
Customer Care Center : 1-800-435-2121
Web : www.tesensors.com

Technical Information:

Detecting Distance: 10.0 mm (0.39 in)
 Circuit Type: 2 wire
 Output Mode: NO
 Volts Type: AC/DC
 Voltage Range: 24-240
 Max Load: AC:350 mA DC:200 mA
 Shielding: Shielded
 Max Switching Frequency: 6000 Hz
 Temp Range: -25° to 70° C (-13° to 158° F)
 NEMA Type: 4X (indoor use only)
 IP Rating: IP67
 Standards: UL, CE Rohs

Specification:

Sensor Type: Inductive
 Description: Proximity Sensor, Inductive, 30 mm Barrel, 24-240, Shielded
 Body Style: Barrel
 Diameter: mm
 Housing Material: Nickel Plated Brass
 Cable Size: 2.0 m (6.6 ft)
 Connector Type:
 Special Features: Motion Detection Sensor