


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XVC4B1K



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

UL File: E164353 CCN NKCR
 CSA File: LR44087 Class 3211-03
 CE Marked: Yes
 RoHS compliant: Yes
 NEMA / IP Rating: NEMA 3R/12 - IP 54

Specification:

Description:
 Size: 40mm diameter
 Housing Color: Red
 Lens Color: Red
 Bulb Color:
 Supply Voltage: 24V AC/DC
 Signaling Effect: Steady Light (Integral LED) w/o buzzer
 Mounting Type: Base
 Terminal Type:
 Cable Length: 900mm
 Comments: Pre-Wired and Pre-Assembled