


**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**XVC6B25S**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

UL File: E164353 CCN NKCR  
 CSA File: LR44087 Class 3211-03  
 CE Marked: Yes  
 RoHS compliant: Yes  
 NEMA / IP Rating: NEMA 3R/12 - IP 54

**Specification:**

Description:  
 Size: 60mm diameter  
 Housing Color: Red and Orange  
 Lens Color: Red and Orange  
 Bulb Color:  
 Supply Voltage: 24V AC/DC  
 Signaling Effect: Steady or Flashing Light (Integral LED) with buzzer  
 Mounting Type: Support Tube  
 Terminal Type:  
 Cable Length: 550mm  
 Comments: Pre-Wired and Pre-Assembled