



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**ZARB18H**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Inputs: 18 digital (12 Limiters + 6 Alarm)  
 Outputs: 20 (18 relay + 2 safety relay)  
 Communication: Wireless : Bluetooth low energy  
 Operating Frequency: 2.4GHz  
 Typical Sensing Distance (Ind. Set.): 50m  
 Maximum Sensing Distance: 100m (unobstructed)

Description:  
 IP Protection:  
 Operating Temperature.:  
 Storage Temperature:  
 Electrical Durability:  
 Mechanical Durability:

**Specification:**

BASE 18 RELAYS PLUS 2 SAFE INDUSTRIAL PLUG  
 IP65  
 -25...+70 C  
 -20...+45C  
 100,000 cycles  
 1,000,000 cycles