



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
ZB4BD57

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

| | |
|---------------------------|--------------------------|
| UL Listed: | Yes |
| UL File: | E164353 CCN NKCR |
| CSA Approval: | Yes |
| CSA File: | LR44087 Class 3211 03 |
| CE: | Yes |
| RoHS: | Yes |
| Bezel Material: | Black Anodized Zinc |
| NEMA / IP Rating: | NEMA 1/2/3/4/4X/13; IP66 |
| Key Number: | n/a |
| Key Removal: | n/a |
| Max. # of Contact Blocks: | 6 |
| Button Marking: | none |

Specification:

| | |
|------------------|----------------------------|
| Description: | 22mm 3 Pos Selector Switch |
| Operator Type: | Non-Illuminated |
| Operator Action: | sp ret both to C |
| Button Type: | Standard Handle |
| Bezel Type: | Metal |
| Color: | Black |
| Head Type: | Round |