



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**ZB4BD7**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

UL Listed:	Yes
UL File:	E164353 CCN NKCR
CSA Approval:	Yes
CSA File:	LR44087 Class 3211 03
CE:	Yes
RoHS:	Yes
Bezel Material:	Chromed Zinc
NEMA / IP Rating:	NEMA 1/2/3/4/4X/13; IP66
Key Number:	n/a
Key Removal:	n/a
Max. # of Contact Blocks:	6
Button Marking:	none

**Specification:**

Description:	22mm 3 Pos Selector Switch
Operator Type:	Non-Illuminated
Operator Action:	sp ret L to C
Button Type:	Standard Handle
Bezel Type:	Metal
Color:	Black
Head Type:	Round