


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**ZB5AZ106**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Tightening Torque: 0.8 Nm  
 Light Module Electrical Consumption: n/a  
 CE: Yes  
 RoHS: Yes  
 Contact Configuration: 1 N.O. (Early Close)/1 N.C. (Late Open)  
 Light Module Supply Voltage: n/a

**Specification:**

Description: Base & Contact Block  
 Light Module Type: n/a  
 Light Module Voltage: n/a  
 Ampere Rating: 10A  
 Contact Material: Silver Alloy  
 Terminal Type: Screw Clamp  
 Utilization Category: AC-15; DC-13  
 Used On: ZB5 Plastic Operators