


Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

ZB6ZB42B



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

UL File: E164353 CCN NKCR
 CSA File: LR44087 Class 321103
 CE Marked: Yes
 RoHS: Yes
 NEMA / IP Rating: NEMA 1/2/3/4/4X/12, IP65
 Terminal Type: Quick Connect/Solder Tabs

Specification:

Description:
 Head Type: not applicable
 Style: Protected LED 12/24V
 Bezel Material:
 Color: Red
 Operator Action: n/a
 Operator Type: Illuminated