

Boost your machines and panels with a touch of style and robustness

Harmony, obviously

A touch of style for your electrical panels and machines without compromising on cost

Affordable modern design and flexibility to tailor your machines to your customers' preferences.

Pushbuttons, switches, and pilot lights you can trust

Extremely robust even in severe environments as proven by the compliance to international standards.

New products to enhance operator and process efficiency

With a dual audible and visual alarm, as well as IP69 dust and water resistance, the new Harmony buzzer brings unequalled operator efficiency, even in dusty or wet environments. Furthermore, the new products for explosive atmospheres provide you with solutions that comply with the relevant UL and IEC standards, for gas and dust/fiber.

The most comprehensive industrial pushbutton offer on the market

Get all your pushbuttons, switches, and pilot lights through a large network of distribution partners, reaching 17,000 points of sale worldwide.

Harmony for modern design at an affordable cost

- Harmony Flush XB4/XB5 pushbuttons deliver an attractive design that enhances the look and feel of your control panels and machines
- Tailor your control panels to respond to your customers' tastes as well as operators' needs
- A vibrant color palette energizing your machines' designs
- Better quality of your machines and panels
- Quick and easy installation

Select between plastic and metal offers according to your robustness expectations and environmental needs

- Compliance with international standards (IEC, UL, CSA, CCC, EAC)
- Marine-certified (BV, RINA, LROS, DNV, GL)
- High dust and water resistance level: IP66, IP67, IP69, IP69K, Type 4X
- Operating temperature range of -40 °C to +70 °C
- High impact resistance: up to IK06

New!

Products for explosive atmospheres

- NEC 500 Class 1 Div 2, Class 2 Div 2 and Class 3
- IECEx 60079 and UL 60079, zone 1/2/21/22



Buzzer

- Both buzzer and light can be continuous or intermittent on the same product
- Sound level: 90 dB at 10 cm
- Robust: IP66/67/69/69K

Buzzer

	24 V AC/DC	110/120 V AC/DC	230/240 V AC
Black / non-illuminated	XB5KSB	XB5KSG	XB5KSM
Illuminated red	XB5KS2B4	XB5KS2G4	XB5KS2M4
Illuminated yellow	XB5KS2B8	XB5KS2G8	XB5KS2M8



Flush

Pushbuttons ZB5FAx	
X=1	○
X=2	●
X=3	●
X=4	●
X=5	●
X=6	●

Selector switches ZB5FDx	
X=2	↙
X=3	↘
X=4	↖
X=5	↗

Illuminated pushbuttons ZB5FW3x3	
X=1	○
X=3	●
X=4	●
X=5	●
X=6	●
X=8	●

Pilot lights ZB5FV0x3	
X=1	○
X=3	●
X=4	●
X=5	●
X=6	●
X=8	●



schneider-electric.com/control

Life Is On

Schneider
Electric

35, rue Joseph Monier
F-92505 Rueil-Malmaison Cedex
Phone: + 33 (0) 1 41 29 70 00
Fax: + 33 (0) 1 41 29 71 00
www.schneider-electric.com