

APC Back-UPS Pro 550, IRAM

High performance battery backup and protection for office computers

The Back-UPS Pro provides you with abundant battery backup power, allowing you to work through medium and extended length power outages – *up to 55 minutes!* It also safeguards your equipment from damaging surges and spikes that travel along utility and network lines. The Back-UPS Pro 550 also features automatic voltage regulation (AVR), which instantly adjusts low voltages to safe levels, so you can work indefinitely during over/undervoltage situations. Additional standard features make the Back-UPS Pro the perfect unit to protect your home network, gaming computer, or business' productivity from the constant threat of power problems and lost data.

Product Features:



- 1 Master and Controlled Outlets - automatically turn off two idling peripherals to save electricity and money.
- 2 LCD (Liquid Crystal Display) provides easy to read information about battery and utility conditions.
- 3 Automatic Voltage Regulation corrects over and undervoltages without draining the battery, saving battery power for when you need it most – outages.
- 4 3 “Battery Backup & Surge Protection” outlets keep CPU, monitor and other critical devices running when the power goes out.
- 5 3 “Surge Only” outlets protect printers, fax machines or other equipment without reducing battery capacity.
- 6 Ethernet surge protection guards against power surges traveling on network lines.
- 7 Push button circuit breaker enables quick recovery from overloads.
- 8 Both USB and serial connectivity allow management of the UPS via your computer.
- 9 2 yr warranty .
- 10 Automatic Diagnostic Testing ensures your unit is ready when you need it.
- 11 Auto shutdown software:
 - Gracefully shuts down system when battery is low
 - Records utility power and battery conditions
 - Allows for customized set up of your battery backup

Back-UPS Pro 550 Specifications

Model Number	BR550G-AR
Output	
Output Capacity	550 VA / 330 Watts
Output Voltage / Freq. (utility)	230V +/-15%, 60Hz
Output Voltage / Freq. (battery)	230V +/-8%, 60Hz
Output Connections	6 total IRAM outlets: 3 battery backup & surge 3 surge protection only
Waveform Type	Stepped Approximation to Sine Wave
Input	
Input Voltage / Frequency	230V / 60 Hz
Input Connection	1.83 meter cord with IRAM plug
Surge Protection	
AC Power Surge Protection	All outlets
Data Line Surge Protection	Network line (10/100 /1000 Base-T Ethernet)
Physical	
Unit Dimensions (H x W x D)	310mm x 190mm x 91mm
Unit Weight	6.53 Kg
Shipping Dims. (H x W x D)	442mm x 252mm x 138mm
Shipping Weight	7.71 Kg
Color	Black
UPC Code	731304286882
Battery	
Battery Type	Maintenance-free, sealed lead-acid battery, leakproof
Management	
Alarms	Visual (LCD) and audible alarms
Auto-Shutdown Software	PowerChute Personal Edition (with USB & serial communications)
Safety	
Certification/Approvals	IRAM, TUV-GS, GOST, CE, C-Tick/A-Tick, KETI, TISI

APC by Schneider Electric

132 Fairgrounds Rd
 West Kingston, RI 02892
 Tel: 401-789-5735
 800-800-4272
 Fax: 401-789-3710
 www.apc.com

