

Hoffman Competitive Cross Sheet

Below is a list of products representing current availability of Schneider Electric universal enclosures stocked in the US and the Hoffman equivalents.

Spacial - metal enclosures - wall-mount

Schneider Electric Part Number	Hoffman Part Number Equivalent	Description mm (in)	List Price	Distributor Net (into stock)
NSYS3DC101030	CSD363610, CSD423610, CSD363612 A423610LP, A423612LP, A42368LP	S3DC 1000 (39.4) H x 1000 (39.4) W x 300 (11.8) D	\$ 688.96	\$ 372.73
NSYS3DC10625	CSD362410	S3DC 1000 (39.4) H x 600 (23.6) W x 250 (9.8) D	\$ 363.87	\$ 196.85
NSYS3DC10825	CSD363010, A363008LP, A363010LP, A36H30BLP, A36H30CLP	S3DC 1000 (39.4) H x 800 (31.5) W x 250 (9.8) D	\$ 403.84	\$ 218.48
NSYS3DC10830	CSD363012	S3DC 1000 (39.4) H x 800 (31.5) W x 300 (11.8) D	\$ 411.31	\$ 222.52
NSYS3DC10840	CSD363016	S3DC 1000 (39.4) H x 800 (31.5) W x 400 (15.6) D	\$ 419.54	\$ 226.97
NSYS3DC121030	A483610LP, A483612LP, A48H36CLP	S3DC 1200 (47.2) H x 1000 (39.4) W x 300 (11.8) D	\$ 775.02	\$ 419.29
NSYS3DC12830	CSD483610, CSD483612	S3DC 1200 (47.2) H x 800 (31.5) W x 300 (11.8) D	\$ 655.73	\$ 354.75
NSYS3DC12840	CSD483616	S3DC 1200 (47.2) H x 800 (31.5) W x 400 (15.6) D	\$ 688.52	\$ 372.49
NSYS3DC3215	A1008CH, A8066CHFL, A808CH	S3DC 300 (11.8) H x 200 (7.9) W x 150 (5.9) D	\$ 91.55	\$ 49.53
NSYS3DC3315	A1210CHNF, CSD12126	S3DC 300 (11.8) H x 300 (11.8) W x 150 (5.9) D	\$ 103.30	\$ 55.89
NSYS3DC3320	A12108CHFL, A1210CH	S3DC 300 (11.8) H x 300 (11.8) W x 200 (7.9) D	\$ 110.91	\$ 60.00
NSYS3DC4315	CSD16126	S3DC 400 (15.6) H x 300 (11.8) W x 150 (5.9) D	\$ 112.70	\$ 60.97
NSYS3DC4320	CSD16128	S3DC 400 (15.6) H x 300 (11.8) W x 200 (7.9) D	\$ 125.17	\$ 67.72
NSYS3DC4420	A16148CH, A1614CH, A1614CHNF, CSD16166	S3DC 400 (15.6) H x 400 (15.6) W x 200 (7.9) D	\$ 149.12	\$ 80.67
NSYS3DC5420	A201608LP, A20H16BLP, CSD20168	S3DC 500 (19.7) H x 400 (15.6) W x 200 (7.9) D	\$ 159.50	\$ 86.29
NSYS3DC5425	CSD201610	S3DC 500 (19.7) H x 400 (15.6) W x 250 (9.8) D	\$ 175.61	\$ 95.01
NSYS3DC5520	CSD16206LG, CSD20206, CSD20208	S3DC 500 (19.7) H x 500 (19.7) W x 200 (7.9) D	\$ 181.78	\$ 98.34
NSYS3DC5525	CSD162010, CSD202010	S3DC 500 (19.7) H x 500 (19.7) W x 250 (9.8) D	\$ 210.48	\$ 113.87
NSYS3DC6420	CSD241610, CSD241610, CSD24168, CSD24168	S3DC 600 (23.6) H x 400 (15.6) W x 200 (7.9) D	\$ 167.92	\$ 90.84
NSYS3DC6425	CSD241610	S3DC 600 (23.6) H x 400 (15.6) W x 250 (9.8) D	\$ 187.45	\$ 101.41
NSYS3DC6620	A242408LP, CSD24208, A24H24BLP, CSD20248, CSD20248	S3DC 600 (23.6) H x 600 (23.6) W x 200 (7.9) D	\$ 223.76	\$ 121.05
NSYS3DC6625	A242410LP, CSD242410	S3DC 600 (23.6) H x 600 (23.6) W x 250 (9.8) D	\$ 249.02	\$ 134.72
NSYS3DC6630	CSD242412	S3DC 600 (23.6) H x 600 (23.6) W x 300 (11.8) D	\$ 226.39	\$ 122.48
NSYS3DC7525	**	S3DC 700 (27.6) H x 500 (19.7) W x 250 (9.8) D	\$ 223.61	\$ 120.97
NSYS3DC8620	CSD30248, A302408LP, A30H24BLP	S3DC 800 (31.5) H x 600 (23.6) W x 200 (7.9) D	\$ 250.66	\$ 135.61
NSYS3DC8625	CSD302410, A302410LP	S3DC 800 (31.5) H x 600 (23.6) W x 250 (9.8) D	\$ 273.13	\$ 147.76
NSYS3DC8630	CSD302412	S3DC 800 (31.5) H x 600 (23.6) W x 300 (11.8) D	\$ 316.50	\$ 171.23
NSYS3DC8640	CSD242416	S3DC 800 (31.5) H x 600 (23.6) W x 400 (15.6) D	\$ 332.33	\$ 179.79
NSYS3DC8825	A303008LP, CSD243010, CSD303010	S3DC 800 (31.5) H x 800 (31.5) W x 250 (9.8) D	\$ 384.65	\$ 208.09
NSYS3DC8830	CSD303012	S3DC 800 (31.5) H x 800 (31.5) W x 300 (11.8) D	\$ 404.89	\$ 219.05
NSYCRN106300*	CSD362410, CSD362412	CRN 1000 (39.4) H x 600 (23.6) W x 300 (11.8) D	\$ 365.91	\$ 197.96
NSYCRN108300*	CSD363012	CRN 1000 (39.4) H x 800 (31.5) W x 300 (11.8) D	\$ 373.92	\$ 202.29
NSYCRN22150*	LSC151512, LSC201512, A808CHFL,	CRN 200 (7.9) H x 200 (7.9) W x 150 (5.9) D	\$ 94.91	\$ 51.35
NSYCRN252150*	LSC252015, A1008CHFL	CRN 250 (9.8) H x 200 (7.9) W x 150 (5.9) D	\$ 79.24	\$ 42.87
NSYCRN325150*	LSC302515, A101006CHFL	CRN 300 (11.8) H x 250 (9.8) W x 150 (5.9) D	\$ 83.23	\$ 45.03
NSYCRN33150*	A1210CHNF, CSD12126	CRN 300 (11.8) H x 300 (11.8) W x 150 (5.9) D	\$ 93.91	\$ 50.81
NSYCRN33200*	A12108CHFL, A1210CH	CRN 300 (11.8) H x 300 (11.8) W x 200 (7.9) D	\$ 100.83	\$ 54.55
NSYCRN34200*	**	CRN 300 (11.8) H x 400 (15.6) W x 200 (7.9) D	\$ 116.75	\$ 63.16
NSYCRN43150*	CSD16126	CRN 400 (15.6) H x 300 (11.8) W x 150 (5.9) D	\$ 102.45	\$ 55.43
NSYCRN43200*	CSD16128	CRN 400 (15.6) H x 300 (11.8) W x 200 (7.9) D	\$ 113.79	\$ 61.56
NSYCRN44200*	A16148CH, A1614CH, A1614CHNF, CSD16166	CRN 400 (15.6) H x 400 (15.6) W x 200 (7.9) D	\$ 112.29	\$ 60.75
NSYCRN54150*	A201608LP, A20H16BLP, CSD20168	CRN 500 (19.7) H x 400 (15.6) W x 150 (5.9) D	\$ 131.61	\$ 71.20
NSYCRN54200*	A201608LP, A20H16BLP, CSD20168	CRN 500 (19.7) H x 400 (15.6) W x 200 (7.9) D	\$ 145.00	\$ 78.45
NSYCRN54250*	CSD201610	CRN 500 (19.7) H x 400 (15.6) W x 250 (9.8) D	\$ 159.65	\$ 86.37
NSYCRN55250*	CSD162010, CSD202010	CRN 500 (19.7) H x 500 (19.7) W x 250 (9.8) D	\$ 191.35	\$ 103.52
NSYCRN64200*	CSD241610, CSD241610, CSD24168, CSD24168	CRN 600 (23.6) H x 400 (15.6) W x 200 (7.9) D	\$ 152.65	\$ 82.58
NSYCRN65200*	CSD24208	CRN 600 (23.6) H x 500 (19.7) W x 200 (7.9) D	\$ 170.41	\$ 92.19
NSYCRN65250*	CSD242010	CRN 600 (23.6) H x 500 (19.7) W x 250 (9.8) D	\$ 182.05	\$ 98.49
NSYCRN66200*	A242408LP, CSD24208, A24H24BLP, CSD20248, CSD20248	CRN 600 (23.6) H x 600 (23.6) W x 200 (7.9) D	\$ 203.42	\$ 110.05
NSYCRN66300*	CSD242412	CRN 600 (23.6) H x 600 (23.6) W x 300 (11.8) D	\$ 262.34	\$ 141.93
NSYCRN68300*	**	CRN 600 (23.6) H x 800 (31.5) W x 300 (11.8) D	\$ 268.04	\$ 145.01
NSYCRN75200*	**	CRN 700 (27.6) H x 500 (19.7) W x 200 (7.9) D	\$ 183.24	\$ 99.13
NSYCRN86200*	CSD30248, A302408LP, A30H24BLP	CRN 800 (31.5) H x 600 (23.6) W x 200 (7.9) D	\$ 227.88	\$ 123.28
NSYCRN86250*	CSD302410, A302410LP	CRN 800 (31.5) H x 600 (23.6) W x 250 (9.8) D	\$ 248.30	\$ 134.33
NSYCRN86300*	CSD302412	CRN 800 (31.5) H x 600 (23.6) W x 300 (11.8) D	\$ 287.73	\$ 155.66
NSYCRN88300*	CSD303012	CRN 800 (31.5) H x 800 (31.5) W x 300 (11.8) D	\$ 368.08	\$ 199.13

*CRN line is not direct cross to Hoffman Concept but can be utilized in cases of lower cost needs

**No direct cross but can be utilized depending on dimensions needed

Spacial - stainless-steel enclosures - wall-mount

Schneider Electric Part Number	Hoffman Part Number Equivalent	Description mm (in)	List Price	Distributor Net (into stock)
NSYS3X302515	A121006CHNFSS	304L SS 300 (11.8) x 250 (9.8) x 150 (5.9)	\$ 266.52	\$ 144.19
NSYS3X3215	A1008CHNFSS	304L SS 300 (11.8) x 200 (7.9) x 150 (5.9)	\$ 242.95	\$ 131.44
NSYS3X3315	CSD12126SS	304L SS 300 (11.8) x 300 (11.8) x 150 (5.9)	\$ 290.05	\$ 156.92
NSYS3X4320	CSD161210SS, CSD16128SS	304L SS400 (15.6) x 300 (11.8) x 200 (7.9)	\$ 376.48	\$ 203.68
NSYS3X4420	CSD16166SS, CSD16168SS	304L SS400 (15.6) x 400 (15.6) x 200 (7.9)	\$ 425.42	\$ 230.15
NSYS3X5420	CSD201610SS, CSD20168SS, CSD20166SS	304L SS 500 (19.7) x 400 (15.6) x 200 (7.9)	\$ 474.00	\$ 256.43
NSYS3X6420	CSD202006SS, CSD20208SS, CSD20208SS, CSD24168SS, CSD241610SS	304L SS 600 (23.6) x 400 (15.6) x 200 (7.9)	\$ 527.09	\$ 285.16
NSYS3X6625	CSD202012SS, CSD24208SS, CSD242412SS, CSD24248SS	304L SS 600 (23.6) x 600 (23.6) x 250 (9.8)	\$ 757.20	\$ 409.65
NSYS3X7525	**	304L SS 700 (27.6) x 500 (19.7) x 250 (9.8)	\$ 760.20	\$ 411.27
NSYS3X8625	CSD302410SS, CSD30248SS	304L SS 800 (31.5) x 600 (23.6) x 250 (9.8)	\$ 895.80	\$ 484.63
NSYS3X10830	CSD362412SS, CSD363010SS, CSD363012SS	304L SS 1000 (39.4) x 800 (31.5) x 300 (11.8)	\$ 1,369.80	\$ 741.06
NSYS3X121030	CSD423610, CSD483610SS	304L SS 1200 (47.2) x 1000 (39.4) x 300 (11.8)	\$ 2,511.79	\$ 1,358.88

Spacial - metal mounting plates and accessories

Schneider Electric Part Number	Hoffman Part Number Equivalent	Description mm (in)	List Price	Distributor Net (into stock)
NSYMM1010	A42P42G	Mounting plate 1000 (39.4) x 1000 (39.4)	\$ 183.21	\$ 99.12
NSYMM106	A40P24G	Mounting plate 1000 (39.4) x 600 (23.6)	\$ 93.64	\$ 50.66
NSYMM106WH	A40P24	Mounting Plate 1000 (39.4) x 600 (23.6)	\$ 121.35	\$ 65.65
NSYMM108	A40P30G	Mounting Plate 1000 (39.4) x 800 (31.5)	\$ 124.09	\$ 67.14
NSYMM108WH	A40P30, A36P30	Mounting Plate 1000 (39.4) x 800 (31.5)	\$ 125.08	\$ 67.67
NSYMM1210	A48P42G, A48P36G	Mounting Plate 1200 (47.2) x 1000 (39.4)	\$ 208.43	\$ 112.76
NSYMM128	A48P36G	Mounting Plate 1200 (47.2) x 800 (31.5)	\$ 179.63	\$ 97.18
NSYMM22	**	Mounting Plate 200 (7.9) x 200 (7.9)	\$ 5.02	\$ 2.72
NSYMM2520	A10P8G	Mounting Plate 250 (9.8) x 200 (7.9)	\$ 5.29	\$ 2.86
NSYMM3025	A12P10G	Mounting Plate 300 (11.8) x 250 (9.8)	\$ 7.70	\$ 4.17
NSYMM32	A12P6G	Mounting Plate 300 (11.8) x 200 (7.9)	\$ 7.70	\$ 4.17
NSYMM32WH	A12P6	Mounting Plate 300 (11.8) x 200 (7.9)	\$ 19.80	\$ 10.71
NSYMM33	A12P12G	Mounting Plate 300 (11.8) x 300 (11.8)	\$ 9.33	\$ 5.05
NSYMM33WH	A12P12	Mounting Plate 300 (11.8) x 300 (11.8)	\$ 20.11	\$ 10.88
NSYMM43	A16P10G	Mounting Plate 400 (15.6) x 300 (11.8)	\$ 12.50	\$ 6.76
NSYMM43WH	A16P10	Mounting Plate 400 (15.6) x 300 (11.8)	\$ 32.15	\$ 17.39
NSYMM44	A16P14G	Mounting Plate 400 (15.6) x 400 (15.6)	\$ 17.00	\$ 9.20
NSYMM44WH	A16P14	Mounting Plate 400 (15.6) x 400 (15.6)	\$ 35.53	\$ 19.22
NSYMM54	A20P16G	Mounting Plate 500 (19.7) x 400 (15.6)	\$ 21.51	\$ 11.63
NSYMM54WH	A20P16	Mounting Plate 500 (19.7) x 400 (15.6)	\$ 30.59	\$ 16.55
NSYMM55	A20P20G	Mounting Plate 500 (19.7) x 500 (19.7)	\$ 29.56	\$ 15.99
NSYMM55WH	A20P20	Mounting Plate 500 (19.7) x 500 (19.7)	\$ 38.67	\$ 20.92
NSYMM64	A24P16G	Mounting Plate 600 (23.6) x 400 (15.6)	\$ 21.60	\$ 11.69
NSYMM64WH	A24P16	Mounting Plate 600 (23.6) x 400 (15.6)	\$ 43.44	\$ 23.50
NSYMM65	A24P20G	Mounting Plate 600 (23.6) x 500 (19.7)	\$ 36.23	\$ 19.60
NSYMM66	A24P24G	Mounting Plate 600 (23.6) x 600 (23.6)	\$ 43.09	\$ 23.31
NSYMM66WH	A24P24	Mounting Plate 600 (23.6) x 600 (23.6)	\$ 54.43	\$ 29.45
NSYMM75	**	Mounting Plate 600 (23.6) x 500 (19.7)	\$ 43.20	\$ 23.37
NSYMM75WH	**	Mounting Plate 600 (23.6) x 500 (19.7)	\$ 66.25	\$ 35.84
NSYMM86	A30P24G	Mounting Plate 800 (31.5) x 600 (23.6)	\$ 74.82	\$ 40.48
NSYMM86WH	A30P24	Mounting Plate 800 (31.5) x 600 (23.6)	\$ 75.79	\$ 41.00
NSYMM88	A30P30G	Mounting Plate 800 (31.5) x 800 (31.5)	\$ 99.58	\$ 53.87
NSYAEFPFSC	CMFK	4 steel wall mounting brackets for S3DC	\$ 10.41	\$ 5.63
NSYPFGR	CMFK	4 wall fixing brackets for CRN	\$ 14.20	\$ 7.68
NSYPFCH	CMFKSS	4 Stainless steel wall mounting brackets	\$ 22.10	\$ 11.96

**No direct cross but can be utilized depending on dimensions needed

Thalassa - insulated enclosures

Schneider Electric Part Number	Hoffman Part Number Equivalent	Description mm (in)	List Price	Distributor Net (into stock)
NSYPLM108G	UU108030	7035 WM PLM 1056 (41.6)H x 852 (33.5)W x 350 (13.8)D	\$ 876.53	\$ 474.20
NSYPLM3025G	HJ1210HWPL2LG	7035 WM PLM 308 (12.1)H x 250 (9.8)W x 160 (6.3)D	\$ 142.81	\$ 77.26
NSYPLM43G	HJ1614HWPL2LG	7035 WM PLM 430 (16.9)H x 330 (13.0)W x 200 (7.9)D	\$ 195.00	\$ 105.50
NSYPLM54G	UU504020	7035 WM PLM 530 (20.9)H x 430 (16.9)W x 200 (7.9)D	\$ 250.11	\$ 135.31
NSYPLM64G	UU605025	7035 WM PLM 647 (25.5)H x 436 (17.2)W x 250 (9.8)D	\$ 291.61	\$ 157.76
NSYPLM75G	UU756030	7035 WM PLM 747(29.4)H x 536 (21.1)W x 300 (11.8)D	\$ 414.97	\$ 224.50
NSYPLM86G	UU756030	7035 WM PLM 847 (33.4)H x 636 (25.0)W x 300 (11.8)D	\$ 491.66	\$ 265.99

Schneider Electric USA, Inc.
8001 Knightdale Blvd.
Knightdale, NC 27545
Phone: 919-266-3671

schneider-electric.us/en/product-category/53800

Date: February 2019
Document Number: 9993BR1801R02/19

©2019 Schneider Electric. All Rights Reserved. Schneider Electric | Life Is On is a trademark and the property of Schneider Electric SE, its subsidiaries, and affiliated companies.