



Emergency light exit signs: For safer and faster evacuation



- > **Aesthetics**
- > **Easy to install** in all places
- > The **cheapest in electricity** consumption
- > The **cheapest in maintenance** costs
- > **100%** compliance with standards

The most effective products for evacuation of public places



Meticulous appearance

- 100% Exit Sign products: enhance the aesthetics of the evacuation function.
- Design adapted to all types of installation
- Both discreet and perfectly visible if need be.



Twofold savings

- Low power consumption of LED and cold cathode products
- Long service life of light sources: reduced maintenance.



Maximum efficiency

- Energy: LED products
- Visual: Product installation methods and size, quality of luminous flux
- Maintenance: Self-diagnosis of the light source and battery (LED indicator).



100% certified

- Exit Signs products are fully compatible with the EN 1838 standard in terms of visibility distance and brightness
- Luminous flux not impaired by adding a sticker.



Perfect integration into all types of environment

- Easy installation: embedded in false ceiling, suspended, surface mounted or flag.

No improvisation on safety!

Exit Signs offer

P1108246



Astro Guida The simplest!

- Cold cathode (40,000 h)
- IP42, IK06
- Dimensions (mm): 213 x 261 x (35)
- Visibility: 24 m
- Maintenance-free.

P1108311



Quick Signal The most elegant!

- LED (50 to 100,000 h)
- IP40, IK07
- Dimensions (mm): 235 x 290 x (60)
- Visibility: 28 m

P1103016



Maxi Slim The biggest!

- Cold cathode (40,000 h)
- IP40
- Dimensions (mm): 443 x 644 x (80) or 523 x 804 x (80)
- Visibility: 60 or 80 m