



TERMINAL LUGS			
AMPERES	MAX. WIRE	MIN. WIRE	TYPE
1200	(4)750 KCMIL	(4)#3/0 AWG	75°C AL OR CU

FUSE PROVISIONS			
AMPERES	TYPE	AMPERES	TYPE
1200	CLASS "L"	800	CLASS "L"

* SIDE ENTRY/EXIT MUST MEET ALL APPLICABLE STANDARDS AND CODES.

DUAL DIMENSIONS: INCHES
MILLIMETERS

NOTES:
FINISH - GRAY BAKED ENAMEL - ANSI #49
CSA CERTIFIED - FILE LL-97406-3
UL LISTED - FILE E-154828
ALL NEUTRALS - INSULATED GROUNDABLE (SHIPPED LOOSE)
SUITABLE FOR USE AS SERVICE EQUIPMENT.
SHORT CIRCUIT RATING:
200,000 AMPERES WHEN USED WITH OR PROTECTED BY CLASS L FUSES.
75 LBS MAX FORCE REQUIRED TO OPERATE HANDLE.
FOR NEMA TYPE 3R APPLICATIONS 1/4-20 DRAIN SCREW MUST BE REMOVED.

SEISMIC NOTES:
USE (4) 7/16" DIA GRADE 5 STEEL MOUNTING BOLTS @ HOLES AA
MAX CONFIGURED WEIGHT 370 LB FOR THE PURPOSE OF DETERMINING
SEISMIC ANCHORAGE REQUIREMENTS. FOR ALL OTHER APPLICATIONS,
CONTACT SQUARE D COMPANY.

CATALOG NUMBER	VOLTAGE RATINGS	WIRING DIAG.	3 PHASE HORSEPOWER RATINGS						DC HORSEPOWER RATINGS			
			240VAC		480VAC		600VAC		250VDC		600VDC	
			STD	MAX.	STD	MAX.	STD	MAX.	STD	MAX.	STD	MAX.
H328	240VAC;250VDC	A	100	250	-	-	-	-	50	50	-	-
H328R	240VAC;250VDC	A	100	250	-	-	-	-	50	50	-	-
H328N	240VAC;250VDC	B	100	250	-	-	-	-	50	50	-	-
H328NR	240VAC;250VDC	B	100	250	-	-	-	-	50	50	-	-
H368	600VAC;600VDC	A	100	250	200	500	250	500	-	-	50	50
H368R	600VAC;600VDC	A	100	250	200	500	250	500	-	-	50	50
H368N	600VAC;600VDC	B	100	250	200	500	250	500	-	-	50	50
H368NR	600VAC;600VDC	B	100	250	200	500	250	500	-	-	50	50
HU368	600VAC;600VDC	C	100	100	-	500	-	500	-	-	50	50
HU368R	600VAC;600VDC	C	100	100	-	500	-	500	-	-	50	50

HEAVY DUTY SAFETY SWITCHES - SEISMIC
VISIBLE BLADE TYPE
1200 AMPERE
ENCLOSURE - NEMA TYPE 1 GENERAL PURPOSE
NEMA TYPE 3R RAINPROOF, NEMA TYPE 5 DUST TIGHT (INDOOR)



DWG# 1940S
NO.