



TERMINAL LUG DATA

AMPERES	MAX WIRE	MIN WIRE	TYPE
30	#8 AWG	#14 AWG	CU
	#8 AWG	#12 AWG	AL

KNOCKOUTS

SYMBOL	A	B	C
CONDUIT SIZE	.50	.75	1

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	VOLTAGE RATINGS	FUSE TYPE	AMPERAGE RATING	WIRING DIAGRAM	HORSEPOWER RATINGS			
					120VAC		240VAC	
					STD	MAX	STD	MAX
L111N	120VAC	PLUG	30	A	1/2	2	-	-
L211N •	120/240VAC	PLUG	30	B	-	-	1 1/2	3
L221N •	120/240VAC	CARTRIDGE	30	B	-	-	1 1/2	3

NOTES: FINISH - GRAY POWDER COAT ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-2875
ALL NEUTRALS - INSULATED.
NOT SUITABLE FOR USE AS SERVICE EQUIPMENT
SHORT CIRCUIT CURRENT RATINGS:
10,000 AMPERES WITH CLASS H FUSES.
FOR SINGLE PHASE HP RATINGS USE 2 SWITCHING POLES.

LIGHT DUTY SAFETY SWITCHES
VISIBLE BLADES
30 AMPERE
ENCLOSURE - NEMA TYPE 1 GENERAL PURPOSE



DWG# 2069
NO.