



PILOT LIGHT

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER: 2510 FF/FS
 RATINGS: 1 HP
 UL FILE/CCN: E42243, CCN NLRV
 CSA FILE/CLASS: LR25490 CLASS 3211 05
 WEIGHT: 2.5 LBS
 WIRE SIZE: #10
 TERMINAL TORQUE: 20 LBS IN.

DEVICE	TYPE OF OPERATOR	CLASS	TYPE	DIMENSIONS			
				A	B	C	D
TWO STARTERS	TOGGLE	2510	FF22, FF22P	5.25	3.75	5.25	1.44
			FS22P	4.56	3.50	4.50	1.44
	KEY	2510	FF44P	5.25	3.75	5.25	1.44
			FS44P	4.56	3.50	4.50	1.44
ONE STARTER AND ONE SELECTOR SWITCH	TOGGLE	2510	FF71, FF71P, FF72, FF72P	5.25	.75	5.25	2.00
			FS71P, FS72P	4.56	3.50	4.50	2.00
	KEY	2510	FF74P	5.25	3.75	5.25	2.00
			FS74P	4.56	3.50	4.50	2.00

NEMA FRACTIONAL HORSEPOWER
 MANUAL STARTERS
 2510_FF_FS_FLUSH MOUNT



DWG# 25100004
 NO.