



KNOCKOUTS

SYMBOL	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	.50	13	.88	22
B	.75	19	1.13	29
C	1	25	1.38	35

EQUIPMENT GROUND TERMINALS

MAX WIRE	MIN. WIRE	TYPE
(1) #4	(1) #14	AL/CU

LINE/LOAD TERMINALS

MAX WIRE	MIN. WIRE	TYPE
(1) #3	(1) #14	AL/CU

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	AMPERE	VOLTAGE RATINGS	HORSEPOWER RATINGS
			240VAC MAX.
+ FP222R	60	240VAC	10

NOTES: UL LISTED - FILE #E131815
 CSA CERTIFIED - FILE #LR48755-25
 + WHEN MOUNTING THESE DISCONNECTS, ALLOW 1.00" CLEARANCE ON HINGE SIDE FOR DOOR TO OPEN.
 SUITABLE FOR USE ON SYSTEMS WITH UP TO 10K RMS SYMMETRICAL
 AMPERES AVAILABLE FAULT CURRENT AT 240VAC.

AIR CONDITIONING DISCONNECTS
 PULL-OUT TYPE
 FUSIBLE - 60 AMPERES
 ENCLOSURE - SIDE OPENING NEMA TYPE 3R



DWG. NO. 3001