





KNOCKOUTS		
SYMBOL	CONDUIT SIZE	
	IN	MM
A	.50	13
B	.75	19
C	1.00	25
D	1.25	32
E	1.50	38
F	2.00	51
G	2.50	64



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO112L200GRB	120/240VAC 1Ø 3W	200	12	12	#4-250
QO12030M150RB		150	20	30	
QO12040M200RB		200	20	40	

NOTES:
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
 UL LISTED - FILE E-6294
 NEUTRALS - INSULATED GROUNDABLE.
 LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE A FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.
 WHEN MOUNTING THESE LOAD CENTERS, ALLOW 1.25 INCHES (32 MILLIMETERS) OF CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN

QO LOAD CENTERS
 RAINPROOF NEMA TYPE 3R ENCLOSURES
 SIDE HINGED OUTDOOR

SQUARE D
 by Schneider Electric

DWG# 3050
 NO.