



DETAIL "A"

DUAL DIMENSIONS: INCHES  
MILLIMETERS

POWER OUTLET CONFIGURATION	SERVICE	MAINS AMPERE RATING	CIRCUIT BREAKER (INCLUDED)	RECEPTACLES (INCLUDED) *	CATALOG NUMBER	MAIN WIRE SIZE AWG			
						PHASE AND NEUTRAL		EQUIPMENT GROUND	
						CU	AL	CU	AL
	120VAC 1Ø 2W	75	(1) Q0120GF1 (2) Q0130	(2) 30A 125V 2W AND GRD. (1) 20A 125V AND GRD. DUPLX NEMA 5-20R	PAK61PG	(2) #6-250		(2) #10-2/0 CU OR (2) #6-2/0 AL	
	120VAC 1Ø 2W	75	(1) Q0120GF1 (2) Q0130GF1	(2) 30A 125V 2W AND GRD. (1) 20A 125V AND GRD. DUPLX NEMA 5-20R	PAK61PGF1	(2) #6-250		(2) #10-2/0 CU OR (2) #6-2/0 AL	
	120/240VAC 1Ø 3W	100	(1) Q0120GF1 (1) Q0130 (1) Q0250-5212	(1) 50A 125/250V 3W AND GRD. NEMA 14-50R (1) 30A 125V 2W AND GRD. (1) 20A 125V 2W AND GRD. DUPLX NEMA 5-20R	PAK75PG	(2) #6-250		(2) #10-2/0 CU OR (2) #6-2/0 AL	
	120/240VAC 1Ø 3W	100	(1) Q0120GF1 (1) Q0130GF1 (1) Q0250-5212	(1) 50A 125/250V 3W AND GRD. NEMA 14-50R (1) 30A 125V 2W AND GRD. (1) 20A 125V 2W AND GRD. DUPLX NEMA 5-20R	PAK75PGF1	(2) #6-250		(2) #10-2/0 CU OR (2) #6-2/0 AL	

NOTES:  
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.  
 UL LISTED - FILE E-53303  
 NEUTRAL - NO BONDING PROVISIONS.  
 SUITABLE FOR USE AS RECREATIONAL VEHICLE SITE SERVICE ENTRANCE EQUIPMENT.  
 ▲ TWO WIRES EACH PER PHASE, NEUTRAL, AND EQUIPMENT GROUND - FOR LOOP-FEED.  
 \* 20 AMPERE RECEPTACLES PROTECTED BY 20 AMPERE GF1 BREAKER.

SERVICEPAK® POWER OUTLET PANELS  
 RAINPROOF NEMA TYPE 3R ENCLOSURE  
 OUTDOOR

**SQUARE D COMPANY**

DWG. NO. **3060**