



KNOCKOUTS		
SYMBOL	IN	MM
A	.50	13
B	.75	19
C	1.00	25

EQUIPMENT GROUND TERMINALS
(6) #14 - #4 AL/CU

LINE/LOAD TERMINALS
#14 - #3 AL/CU

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	AMPERE	FUSIBLE/NOT FUSIBLE	VOLTAGE RATINGS	WIRING DIAGRAM	HORSEPOWER RATINGS 240VAC MAX
+ UFP222RNM ●	60	NF	240VAC	B	10
+ FP222RNM ▲	60	F		A	10
+ FP221RNM ▲	30	F		A	3

- NOTES:
UL LISTED
+ WHEN MOUNTING, ALLOW 1.00IN / 25MM CLEARANCE ON HINGE SIDE FOR DOOR TO OPEN.
▲ SUITABLE FOR USE ON SYSTEMS WITH UP TO 10K RMS SYMMETRICAL AMPERES AVAILABLE FAULT CURRENT AT 240VAC
● SUITABLE FOR USE ON SYSTEMS WITH UP TO 10K RMS SYMMETRICAL AMPERES AVAILABLE FAULT CURRENT AT 240VAC MAX WHEN PROTECTED BY A FUSE OR CIRCUIT BREAKER RATED 60 AMPERES OR LESS.

AIR CONDITIONING DISCONNECTS
PULL-OUT TYPE
FUSIBLE - 30 AND 60 AMPERES
NOT-FUSIBLE - 60 AMPERES
ENCLOSURE - SIDE OPENING NEMA TYPE 3R
NON-METALLIC

SQUARE D COMPANY

DWG. NO. 3105