





KNOCKOUTS		
SYMBOL	IN	MM
A	.50	13
B	.75	19
C	1.00	25
D	1.25	32
E	1.50	38



QO1DM10020TRBR



QO1DM10030TRBR



QO1DM10050TRBR

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	GENERATOR MAIN	POWER INLET TYPE	RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUIT	MAIN WIRE SIZE AWG AL/CU
QO1DM10020TRBR QO1DM10030TRBR QO1DM10050TRBR	120/240 VAC 1Ø3W	100A	20 A 30 A 50 A	NEMA L14-2 NEMA L14-30P HUBBELL CS6375	20 A 30 A 50 A	4	8	#6-2

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.
UL LISTED - FINE E-6294
NEUTRALS - INSULATED GROUNDABLE.

QO LOAD CENTERS
RAINPROOF NEMA TYPE 3R ENCLOSURE
OUTDOOR



DWG# 3449
NO.