




EXPORT MODEL TRANSFORMER  
 1.0 KVA 1Ø 50/60HZ  
 110/220V SECONDARY



SIDE VIEW




FRONT VIEW




BOTTOM VIEW

NOTES:  
 UL/CUL LISTED  
 CE MARKED .750 KVA PER EN60-742  
 NEMA 3R NON-VENTILATED ENCLOSURE  
 IP54 NON-VENTILATED ENCLOSURE  
 COPPER WOUND  
 185°C INSULATION SYSTEM FOR 115°C RISE  
 EPOXY-RESIN ENCAPSULATED  
 USE TERMINAL BLOCK COVER KIT 7400ENT9 TO MEET TOUCH-SAFE REQUIREMENTS OF EN60-204



PARALLEL CONNECTION



SERIES CONNECTION

PARALLEL PRIMARY		
HIGH VOLTAGE	LINES CONNECT	CONNECT TOGETHER
190	H1 & H7	H1 - H6 H2 - H7
200	H1 & H8	H1 - H6 H3 - H8
208	H1 & H9	H1 - H6 H4 - H9
220	H1 & H10	H1 - H6 H5 - H10

SERIES PRIMARY		
HIGH VOLTAGE	LINES CONNECT	CONNECT TOGETHER
380	H1 & H7	H2 - H6
400	H1 & H8	H3 - H6
416	H1 & H9	H4 - H6
440	H1 & H10	H5 - H6

DUAL DIMENSIONS: INCHES  
 MILLIMETERS

KVA	CATALOG NUMBER	GUAR. SOUND LEVEL	WGT LBS
1.0	1S67F	40 DB	21.2

EXPORT MODEL TRANSFORMER  
 1.0 KVA 1Ø 50/60HZ  
 110/220V SECONDARY

**SQUARE D COMPANY**

DWG. NO. 3591