




NON-VENTILATED DRY-TYPE TRANSFORMERS
25-37.5 KVA 1Ø 60HZ
120/240V SECONDARY




480 VOLT PRIMARY CONNECT H2 TO H3 CONNECT LINES TO H1, H4	
PRIMARY VOLTS	CONNECT TO TAPS
504	1 AND 8
492	1 AND 7
480	2 AND 7
468	2 AND 6
456	3 AND 6
444	3 AND 5
432	4 AND 5



SERIES CONNECTION
480 VOLT CONNECTION



240 VOLT PRIMARY CONNECT H1 TO H3, H2 TO H4 CONNECT LINES TO H1 & H4	
PRIMARY VOLTS	CONNECT TO TAPS
252	1 AND 8
240	2 AND 7
228	3 AND 6
216	4 AND 5



PARALLEL CONNECTION
240 VOLT CONNECTION

DUAL DIMENSIONS: INCHES
MILLIMETERS

KVA	CATALOG NUMBER	GUAR. SOUND LEVEL	WGT LBS	AV % Z
25	25S3HNV	45 DB	310	3.1
37.5	37S3HNV	45 DB	350	4.5

- NOTES:
 NEMA 3R NON-VENTILATED ENCLOSURE
 ALUMINUM WOUND
 220°C INSULATION SYSTEM FOR 150°C RISE
 ● WALL MOUNTING BRACKET WMB363-364
 ▲ SPACE AVAILABLE IN BOTTOM FOR CUSTOMERS CONDUIT ENTRANCE.
 ‡ SPACE AVAILABLE ON BOTH ENDS FOR CUSTOMERS CONDUIT.

NON-VENTILATED DRY-TYPE TRANSFORMERS
25-37.5 KVA 1Ø 60HZ
120/240V SECONDARY



DWG. No. 3623