


SWITCH RATINGS

RATED MAX. VOLTAGE:	4.76 KV 15.0 KV
IMPULSE WITHSTAND:	60KV 95 KV
FREQUENCY:	50 / 60 Hz
CONTINUOUS CURRENT:	600A
LOAD INTERRUPTING CURRENT:	600A
MOMENTARY CURRENT:	61 KA ASYM.
FAULT CLOSE CURRENT:	40 KA ASYM.
WEIGHT:	1350 LBS. APPROX

LUGS
LINE LOAD & GROUND: #2 - 600 MCM (SET SCREW)

OUTLINE APPLICABLE FOR CAT. NO.:
HVL305NG - 4.76KV
HVL315NG - 15.0KV

OUTLINE - HVL SWITCHGEAR INDOOR
4.76 & 15.0 KV, UNFUSED

 **SQUARE D COMPANY**

DWG# 44040-024
No.