



TOP VIEW

KNOCKOUTS NOT INCLUDED IN THE TOP OF UL TYPE 3R ENCLOSURES. TOP CONDUIT ENTRY IS NOT RECOMMENDED FOR UL TYPE 3R ENCLOSURES.





TOP VIEW

KNOCKOUTS NOT INCLUDED IN THE TOP OF UL TYPE 3R ENCLOSURES. TOP CONDUIT ENTRY IS NOT RECOMMENDED FOR UL TYPE 3R ENCLOSURES.





TOP VIEW

KNOCKOUTS NOT INCLUDED IN THE TOP OF UL TYPE 3R ENCLOSURES. TOP CONDUIT ENTRY IS NOT RECOMMENDED FOR UL TYPE 3R ENCLOSURES.





CG = CENTER OF GRAVITY FROM MTG SURFACE
7.20 [183]

SIZE C ENCLOSURE




CG = CENTER OF GRAVITY FROM MTG SURFACE
8.00 [203]

SIZE D ENCLOSURE




CG = CENTER OF GRAVITY FROM MTG SURFACE
5.10 [130]


SIZE D ENCLOSURE




BOTTOM VIEW




DOOR PROJECTION




BOTTOM VIEW



DOOR PROJECTION



BOTTOM VIEW



DOOR PROJECTION

DUAL DIMENSIONS: INCHES MILLIMETERS

SIZE C ENCLOSURE
TYPE 1/12K 15-25HP 208V, 20-30HP 230V, 40-60HP 460V, 50-75HP 575V
TYPE 3R 15-20HP 208V, 15-25HP 230V, 30-50HP 460V, 40-60HP 575V

SIZE D ENCLOSURE
TYPE 1/12K 30-50HP 208V, 40-60HP 230V, 75-125HP 460V, 100-150HP 575V
TYPE 3R 25-40HP 208V, 30-50HP 230V, 60-100HP 460V, 75-125HP 575V

OUTLINE DRAWING C & D
ATS22 ENCLOSURE



DWG# 80463-221-00
NO.