


MAXIMUM CURRENT RATING FOR CONTROL CIRCUIT RATINGS

(1) TYPE	VOLTS	AC AMPERES			VOLTS	DC AMPERES		
		INDUCTIVE 35% POWER FACTOR	RESISTIVE 75% POWER FACTOR	MAKE BREAK AND CONTINUOUS		INDUCTIVE AND RESISTIVE		
						MAKE SINGLE THROW	BREAK DOUBLE THROW	CONTINUOUS
AW-124	120	60	6	10	125	1.10	-	10
	240	30	3	10	250	.55	-	10
	480	15	1.50	10	600	.20	-	10
	600	12	1.20	10	-	-	-	-

Catalog Number: AW-(1)  
 Ratings: SEE CHART  
 UL File/CCN: -  
 CSA File/Class: -  
 Meets Standards: -  
 Weight: -  
 Wire Size: -  
 Terminal torque: -  
 Mounting Hwd.: -

DUAL DIMENSIONS: INCHES  
MILLIMETERS

FOOT SWITCH 600VAC 10AMP + OPTIONS	 <b>by Schneider Electric</b>
	DWG# 9002AW124 NO.