



Catalog Number: AW-(1)
 Ratings: SEE CHART
 UL File/CCN: -
 CSA File/Class: -
 Meets Standards: -
 Weight: -
 Wire Size: -
 Terminal torque: -
 Mounting Hwd.: -

MAXIMUM CURRENT RATING FOR CONTROL CIRCUIT RATINGS

(1) TYPE	VOLTS	AC AMPERES			VOLTS	DC AMPERES		
		INDUCTIVE 35% POWER FACTOR	RESISTIVE 75% POWER FACTOR	MAKE BREAK AND CONTINUOUS		INDUCTIVE AND RESISTIVE		
						MAKE SINGLE THROW	BREAK DOUBLE THROW	CONTINUOUS
AW-117, AW-119, AW-132	120	40	10	15	125	2	.50	15
	240	20	10	10	250	.50	.20	15
	480	10	6	6	600	.10	.02	15
	600	8	5	5	-	-	-	-
AW-133	120	30	3	3	125	1	.20	10
	240	15	1.50	1.50	250	.30	.10	10
	480	7.50	.75	.75	600	.10	-	10
	600	6	.60	.60	-	-	-	-
AW-123	120	30	1.50	10	-	-	-	-
	240	15	.75	10	-	-	-	-
	480	7.50	3.75	10	-	-	-	-
	600	6	.30	10	-	-	-	-

DUAL DIMENSIONS: INCHES
MILLIMETERS

FOOT SWITCH 600VAC 5AMP + OPTIONS



DWG# 9002AW132
NO.