


CABLE LENGTH	BOX DEPTH MAX.	MAX. DISTANCE FROM TOR RIGHT MTG. HOLE TO UPPER MTG. HOLE FOR HANDLE OPERATOR
36.00	24.00	7.00
60.00	36.00	24.00
120.00	36.00	60.00

Minimum to wall or barrier to insure adequate wire bending space to lug surface when the maximum wire size is used with standard lugs. REF NEC 430-10



Catalog Number: 9422-CFA30, CFA50, CFA10
 Ratings: for use with FAL, & FHL CIRCUIT BREAKERS
 UL File/CCN: E62922 DIHS2
 CSA File/Class: N/A
 Meets Standards:
 Weight: 5.50 lbs.
 Wire Size: -
 Terminal torque: -
 Mounting Hwd: (4)-#8-32 screws

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

DO NOT SCALE DRAWING
 UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION
 TOLERANCES
 UNLESS OTHERWISE SPECIFIED
 2 PLACE DECIMALS ± .01

OPERATING MECHANISM
 FOR USE WITH FAL & FHL CIRCUIT BREAKERS
 CLASS 9422 TYPES CFA30, CFA50, CFA10

SQUARE D COMPANY

DWG# 9422_CFA_OUTLINE_001
 NO.