



ELECTRICAL CLEARANCE/WIRE BENDING SPACE

12.00
[305]

MINIMUM TO WALL OR BARRIER TO INSURE ADEQUATE
WIRE BENDING SPACE TO LUG SURFACE WHEN
THE MAXIMUM WIRE SIZE IS USED
WITH STANDARD LUGS. REF NEC 4-30-10



NEMA SIZE 6 STARTER
3-POLE POLYPHASE - 600 VAC, 50-60 HZ

CDL VOLTAGE CODE (1)	VOLTAGE	
	60 HZ	50 HZ
V02	120	110
V08	208	-
V03	240	220
V06	480	440
V07	600	550
V99	SPECIFY	SPECIFY

Catalog Number: 8536-SH02(1)
 Ratings: SEE CHART
 UL File/CCN: E78361/NLDX
 CSA File/Class: LR80906/3211 0
 Meets Standards: -
 Weight: 85.00 lbs
 Wire Size: POWER - (1 or 2)250NCM-500NCM | CONTROL - #18-#12
 Terminal torque: 375 LB/IN
 Mounting Hwd.: (3) 1/2" screws

DUAL DIMENSIONS: INCHES
MILLIMETERS

NEMA SIZE 6 STARTER
CLASS 8536 TYPE SH02(1)



DWG# E0303501-01
NO.