



TYPE CODE {1}	CONVERTIBLE CONTACTS 1 N.O., 1N.C.
00XTE(*)	0
20XTE(*)	2
40XTE(*)	4
00XTD(*)	0
20XTD(*)	2
40XTD(*)	4

□ = OFF DELAY TIMING MODE

TIMING RANGES

TYPE CODE (*)	TIMING RANGE
1	0.2-60 SEC.
2	5-180 SEC.

VOLTAGE CODES

VOLTAGE CODE {2}	AC VOLTAGES
V11	12VAC - 60HZ
VD1	24VAC - 60HZ
V12	24VAC - 50HZ
V18	48VAC - 60HZ
V1B	48VAC - 50HZ
VD2	110/120VAC - 50/60HZ
VD8	208VAC - 60HZ
VD3	220/240VAC - 50/60HZ
VD4	277VAC - 60HZ
VD8	440/480VAC - 50/60HZ
VD7	550/600VAC - 50/60HZ

TYPE X MOUNTING TRACK

Catalog Number: 8501-XQ(1)(2)  
 Ratings: 800V, 10A  
 UL File/DCN: E78403/NKGR  
 CSA File/Class: LR60905/3211 03  
 Meets Standards: -  
 Weight: 2.7 lbs  
 Wire Size: #12-#18 AWG  
 Terminal torque: 9-11 LB/IN  
 Mounting Hvd.: {2} #8-32 SCREWS, TYPE X MOUNTING TRACK

DUAL DIMENSIONS: INCHES  
 MILLIMETERS

AC TIMING RELAY (4 POL3)  
 CLASS 8001 TYPE XQ(1) TE(2)



DWG# E0700801-01  
 NO.