




TOP VIEW




BACK VIEW



FRONT VIEW



BOTTOM VIEW



RIGHT VIEW

VARIABLE TIME DELAY

KNOB ADJUSTABLE TIMING RANGE	CODE (1) REPEAT CYCLE
0.1-10 SEC	51
0.3-30 SEC	52
0.6-60 SEC	53
1.2-120 SEC	54
1.8-180 SEC	55
0.1-10 MIN	56
0.3-30 MIN	57
0.6-60 MIN	58
1.2-120 MIN	59

VOLTAGE CODES

VDLTS	CODE (2)
12 VAC/DC	V36
24 VAC/DC	V14
48 VAC/DC	V17
120 VAC/110 VDC	V20

CONTACT ARRANGEMENT: DPDT (2NO & 2NC)
CONTINUOUS CURRENT RATING: 10A

NOTE: A RETAINING STRAP DESIGNED TO HOLD TIMER IN SOCKET DURING HEAVY VIBRATION IS AVAILABLE WITH PN#8501-NH7.

AC VOLTS	AC AMPS			RES. 75% PF MAKE BREAK AND CON-TINUOUS	HP	DC VOLTS	DC AMPS			
	INDUCTIVE 35% PF	MAKE	BREAK				CON-TINUOUS	INDUCTIVE		RES. MAKE BREAK AND CON-TINUOUS
								MAKE	BREAK	
120	3D	3	10	10	1/3	30	3	3	10	
240	1.5	1.5	10	10	1/2					

Catalog Number: 9050-JCK(1)(2)
 Ratings: SEE CHART
 UL File/CCN: CCN-E42240-NLDX2
 CSA File/Class: LR25480-3211-04
 Meets Standards: -
 Weight: -
 Wire Size: -
 Terminal torque: -
 Mounting Hwd.: -

DUAL DIMENSIONS: INCHES
MILLIMETERS

GENERAL PURPOSE PLUG-IN TIMER (8 PIN)
9050-JCK(1)(2)



DWG# E0703301-01
NO.