



DIMENSIONS SHOWN IN INCHES AND [MILLIMETERS]  
ALL DIMENSIONS ARE REFERENCE ONLY



FOR INFORMATION  
ONLY. NOT FOR  
MANUFACTURE,  
PRODUCTION,  
OR QUOTING

CATALOG NUMBER: SINGLE PACK 8501NR62  
BULK PACK 8501NR62B  
RATINGS: UL 16AMP-300V  
5AMP-600V  
CSA 10AMP-300V  
20AMP MAX. TOTAL LOAD  
UL FILE/CCN E66924/SWIV2  
CSA FILE/CLASS 211268/3211 07  
STANDARDS MET CE AND RoHS  
WEIGHT 2.8 OUNCES/79 GRAMS  
WIRE SIZE #12-22 AWG  
TIGHTENING TORQUE 7-8 LB-IN  
MOUNTING DIN3 TRACK MOUNTING OR DIRECT PANEL MOUNTING

DUAL DIMENSIONS: INCHES  
MILLIMETERS

11 PIN OCTAL SOCKET  
8501 NR62



DWC# E0704101-01  
No.