



- NOTES:
 1) UL TYPE 1 ENCLOSURE
 2) AMBIENT TEMP 0-45 C
 3) ALTITUDE 1000 m (3300 FT)
 4) HUMIDITY 95% NON-CONDENSING
 5) MINIMUM CLEARANCE 200 mm TOP AND BOTTOM

GDE29549 ACCUSINE PCSN 60A 208-415V UL T1 EXP 1 PCSN060Y4N1E

	Scale: N/A	Tolerancing Standard: ISO8015	Units of Measure: mm
	ACCUSINE PCSN UL TYPE 1EXP ACCUSINE PCSN UL TYPE 1EXP		
	Number: GDE2954901	Revision: 00	Sheet: 1 OF 1

All information and data contained in this document are the exclusive property of Schneider Electric Industries SAS and may neither be used nor disclosed without its prior written consent.

State: