



NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL CODES.
2. SEE PRODUCT DOCUMENTATION FOR FURTHER INFORMATION.
- △ 3. THESE CONNECTIONS ARE APPLICABLE TO APC XR ENCLOSURE ONLY.
4. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.
5. PLEASE REFER TO INSTALLATION MANUAL FOR DETAILS.
6. USE ONLY 1-1.5SQMM COPPER WIRE FOR EPO CONNECTION.
7. CABLING PROVIDED BY OTHERS.
8. OUTPUT OVERCURRENT PROTECTION SHALL BE PROVIDED BY OTHERS. RECOMMENDED OUTPUT BREAKER RATING 10KVA-16A, 15KVA-25A, 20KVA-35A, 30KVA-50A, 40KVA-63A.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: SMART-UPS VT 10-40KVA WITHOUT MAINTENANCE BYPASS PANEL 230VAC CONTROL VOLTAGE WIRING DIAGRAM

PROJECT: STD SUBMITTAL DRAWINGS SHEET 1 OF 1

DWG NO: SUVTP10K40H-WD REV. 2

DRAWN BY:	V BUSH	28-MAR-11	PROJ
ENGINEER:	M SALOKHE	28-MAR-11	ANGLE
APPROVED BY:	S WAGH	28-MAR-11	N.A.