



NOTES:

- PLEASE REFER TO INSTALLATION MANUAL FOR DETAILS
- USE ONLY 1-1.5sqmm COPPER WIRE FOR EPO CONNECTION
- △ 3. THESE CONNECTIONS ARE APPLICABLE TO APC XR ENCLOSURE ONLY
- CABLING PROVIDED BY OTHERS
- OUTPUT OVERCURRENT PROTECTION MUST BE PROVIDED BY OTHERS.
RECOMMENDED OUTPUT BREAKER RATING
10kVA-16A, 15kVA-25A, 20kVA-35A, 30kVA-50A, 40kVA-63A
- INSTALLATION MUST COMPLY WITH ALL NATIONAL AND LOCAL ELECTRICAL REGULATIONS.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF AMERICAN POWER CONVERSION AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM APC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.		TITLE: SMART-UPS VT 10-40kVA WITHOUT MAINTENANCE BYPASS PANEL 230VAC CONTROL VOLTAGE SYSTEM WIRING DIAGRAM		DWG NO: SUVT10K40H-WD		REV. 1		 AMERICAN POWER CONVERSION 132 FAIRGROUNDS RD WEST KINGSTON, RI 02892
PROJECT: SUBMITTAL DRAWING		SHEET 1 OF 1		ENGINEER: C LARSEN		11/10/05		
				DRAWN: C KRISHNA		11/10/05		