



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

LGF36250-Electronic



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Certification: UL Listed, CSA, IEC Rated
 Mounting Type: On = terminal nut, OFF= terminal nut
 Weight: 15
 AL Lug Wire Size A,L,M,P: N/A
 Depth:
 Height:
 Width:

Specification:

Description: Unit Mount – 3 Pole Molded Case Circuit Breaker
 General Application: Provides overload and short circuit protection
 For Use With: Industrial Panelboards and Switchboards
 Voltage Rating: 600Vac Max
 Ampere Rating: 250A
 Electronic Trip Unit Function: LI, LS, LSI, or LSIG
 Number of Poles: 3
 Short Circuit Current Rating: 65/35/18 kA UL and IEC ratings
 Circuit Breaker Rating: Standard 80%