



LEFT VIEW


.56/[14] SLOT
TYPICAL 4 PLACES




FRONT VIEW



TOP VIEW



DOOR PROJECTION



BOTTOM VIEW

1HP [.75KW] – 15HP [11KW] AT 460V NORMAL DUTY*
 .5HP [.37KW] – 10HP [7.5KW] AT 460V HEAVY DUTY*
 1HP [.75KW] – 7.5HP [5.5KW] AT 230V NORMAL DUTY*
 .5HP [.4KW] – 5HP [4KW] AT 230V HEAVY DUTY*

*STANDARD DRIVE PACKAGE

DUAL DIMENSIONS: INCHES
MILLIMETERS

ALTIVAR PROCESS
660 DRIVE SYSTEM – OUTLINE



DWG# NHA3293902
NO.