




REV	DESCRIPTION	BY	DATE					
---	---	---	---	---	---	---	---	---




**TYPICAL BOX WITH INTERIOR**




**TYPICAL BOX SIDE VIEW**



**TYPICAL FRONT**



**TYPICAL MOUNTING OF QO OR QOB BREAKERS**



**BOTTOM ENDWALL CUTOUT**

REFER TO DP CATALOG CLASS 1630 FOR ADDITIONAL INFORMATION

MPS NQ MB PANELBOARDS ARE UL LISTED.

BOX: CODE GAUGE GALVANIZED STEEL. TOP ENDWALL WILL BE BLANK AND BOTTOM ENDWALL HAS A CUTOUT.

FRONT: MONO-FLAT CONSTRUCTION WITH TRIM SCREWS AND DOOR HINGES. ANSI 49 GRAY BAKED ENAMEL FINISH ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL. SOME TRIMS WILL BE VENTED.

LOCK: FLUSH LOCK WITH BRUSHED, STAINLESS STEEL ESCUTCHEON. NSR-251 KEY CHANGE.

DUAL DIMENSIONS: INCHES MILLIMETERS

TYPE	AMPS	MLO/MB	CKT	NON-MPS BOX LENGTH		A		B	
				IN	MM	IN	MM	IN	MM
NQ	600	VMB	30	68.00	1727	63.00	1600	11.35	288
NQ	600	VMB	42	68.00	1727	63.00	1600	11.35	288
NQ	600	VMB	54	74.00	1880	69.00	1753	8.35	212

JOB NAME: ---	EQUIPMENT DESIGNATION: ---
JOB LOCATION: ---	EQUIPMENT TYPE: NQ FULL HEIGHT 600A VMB
DRAWN BY: ---	DRAWING TYPE: ---
ENGR: ---	
DATE: JULY 2008	
DRAWING STATUS: ---	DWG# PBA582_EN
	PG 01 OF 01
	REV ---