



TRANSFORMER SPECIFICATIONS:
 15KVA 1Ø 60 HZ
 PRIMARY VOLTAGE 480
 SECONDARY VOLTAGE 120/240
 115°C RISE
 185°C INSULATION SYSTEM
 APPROXIMATE WEIGHT: 390 LBS
 GUARANTEED SOUND LEVEL: 45 dB

SEISMIC QUALIFICATION:
 TO BE COMPLIANT WITH THE SEISMIC REQUIREMENTS OF ASCE/SEI 7, THIS UNIT HAS BEEN QUALIFIED BY SHAKE TABLE TESTING THROUGH SELF CERTIFICATION TO ICC ES AC156. CONTACT YOUR LOCAL SQUARE D / SCHNEIDER ELECTRIC REPRESENTATIVE FOR RELATED QUESTIONS.

DUAL DIMENSIONS: INCHES
 MILLIMETERS

- NOTES:
 1) UL LISTED (MEETING UL 1062)
 2) NEMA 3R ENCLOSURE
 3) MINIMUM FIELD CLEARANCES: 12.00/[305] SIDE AND 12.00/[305] VERTICAL
 4) CENTER OF GRAVITY (CG) LOCATED AS SHOWN.

SEALED MINI POWER-ZONE
 TRANSFORMER
 CATALOG NO MPZB25S40F
 1 PHASE, 25 kVA
 PRIMARY 480, SECONDARY 120/240

SQUARE D
 by Schneider Electric

DWG# PWEQP-TRFBC-0025
 NO.