



KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64



QO13842MX200

DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO13842MX150 QO13842MX200 QO13842MX225	120/240VAC, 1Ø3W	150 200 225	38	42	#4 - 250
QO13842UX225		225			

- NOTES:
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
 UL LISTED
 NEUTRALS - INSULATED GROUNDABLE.
 * AUTOMATIC TRANSFER SWITCH AND ALL GENERATOR COMPONENTS MUST BE ORDERED SEPARATELY FROM AN AUTHORIZED KOHLER DEALER OR CONTRACTOR.
 * GENERATOR MAIN CIRCUIT BREAKER (QO125A MAX) ORDER SEPARATELY.

QO LOAD CENTERS
 GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE
 INDOOR



DWG# PWFDS-SYRS-0041
 No.