





OPTIONAL OVERHEAD BARRIER TUNNEL KIT. ORDER CAT NO OHBS WHEN REQUIRED FOR LOAD WIRES TO EXIT TOP ENDWALL. CONSULT UTILITY FOR APPROVAL.




- ONE SINGLE POLE, ONE PLUG-ON SPACE TYPE QO. TWO POLE TYPE QO, QOA, OR QOC (125A MAX) MAY PLUG-ON TWO ADJACENT SPACES. TWO POLE TYPE QOC (150-200A) MAY PLUG ON FOUR ADJACENT SPACES.
- TWO SINGLE POLE, ONE PLUG-ON SPACE TYPE QOT OR ONE SINGLE POLE TYPE QO. TWO POLE TYPES QO, QOA, OR QOC (125A MAX) MAY PLUG-ON TWO ADJACENT SPACES. TWO POLE TYPE QOC (150-200A) MAY PLUG ON FOUR ADJACENT SPACES.

TOTAL CIRCUIT BREAKER HANDLE RATING NOT TO EXCEED 160A PER CIRCUIT CONNECTOR.
A SQUARE D UL LISTED SECONDARY SURGE ARRESTER MAY PLUG ON TWO ADJACENT SPACES. ORDER CATALOG NO QO2175SB.

SYMBOL	KNOCKOUTS			
	CONDUIT SIZE		HOLE DIA	
	IN	MM	IN	MM
A	.50	13	.87	22
B	.75	19	1.12	28
C	1.00	25	1.37	35
D	1.25	32	1.75	44
E	1.50	38	2.00	51
F	2.00	51	2.50	64
G	2.50	64	3.00	76
H	3.00	76	3.62	92



METER COVER LATCH



SEAL BRACKET UTILITY WIREWAY

DUAL DIMENSIONS: INCHES MILLIMETERS

MAINS AMPERE RATING	FACTORY INSTALLED BYPASS TYPE	SHORT CIRCUIT CURRENT RATING	CATALOG NUMBER	SERIES	SPACES	MAXIMUM NUMBER OF SINGLE POLE QO CIRCUITS	LINE SIDE PHASE & NEUTRAL LUGS AWG/KCMIL	SERVICE GROUND LUG AWG
200	HORN	22K	QC3040M200SH	M01	30	40	#6-350 CU/AL	#14-20 CU #12-20 AL
200	NONE	22K	QC3040M200S	M01	30	40	#6-350 CU/AL	#14-20 CU #12-20 AL

NOTES:
FINISH - GRAY BAKED ENAMEL POWDER COAT PAINT OVER CLEANED GALVANNEALED STEEL.
MAXIMUM SYSTEM VOLTAGE: 120/240VAC, 1Ø3W, 50-60HZ, 208Y/120VAC, 1Ø3W, 50-60HZ (FROM A 3Ø4W SYSTEM)
UL LISTED - FILE E-6294, VOL M
SUITABLE ONLY FOR USE AS SERVICE EQUIPMENT.
SUITABLE FOR UNDERGROUND/OVERHEAD SERVICE.

COMBINATION SERVICE ENTRANCE DEVICES
RINGLESS TYPE ALL-IN-ONE QO 30-40 CIRCUIT
RAINPROOF NEMA TYPE 3R ENCLOSURE
SURFACE MOUNT

by Schneider Electric

DWG# PWFDS-SYRS-0049
NO.