


KNOCKOUTS							
SYMBOL	A	B	C	D	E	F	G
IN	.50	.75	1.00	1.25	1.50	2.00	2.50
MM	13	19	25	32	38	51	64

TANDEM BREAKERS - ANY POSITION



DUAL DIMENSIONS: INCHES MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO116M100PRB	120/240 VAC 1Ø 3W	100	16	24	#6-2/0
QO120M100PRB		100	20	24	
QO124M100PRB		100	24	34	
QO124M125PRB		125	24	34	
QO116L125PGRB		125	16	24	
QO124L125PGRB		125	24	34	

NOTES:
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPATIZED STEEL.
 UL LISTED - FILE E-6294
 NEUTRALS - INSULATED GROUNDABLE.
 LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE A FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.
 WHEN MONTING THESE LOAD CENTERS, ALLOW 1.25 INCHES OF CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN.
 LOAD CENTERS WITH "P" IN CATALOG NUMBER INCLUDE EXTENDED NEUTRALS FROM PLUG ON NEUTRAL READY INTERIORS.

QO Plug-on Neutral Load Centers
 RAINPROOF NEMA TYPE 3R ENCLOSURE
 SIDE HINGED
 OUTDOOR

SQUARE D
 by Schneider Electric

DWG# PWFDS-SYRS-0054
 NO.