


		1	2	3	4	5	6	7	8	9	10																	
A	Folio Sheet	Designation Designation			Indice de modification Revision							Folio Sheet	Designation Designation			Indice de modification Revision							A					
	001	FRONT PAGE			00																							
	002	SUMMARY			00																							
	003	FUNCTIONAL PLATE			00																							
	004	LAYOUT			00																							
	005	WIRE LIST			00																							
	006	PART LIST			00																							
B																						B						
C																						C						
D																						D						
Archivage Microfilm					SUMMARY							CELLEAN OFFER									PHA1777503		Projet - No commande Project - Order No.		Indice Rev 00		Folio Sheet 002	



1		2		3		4		5		6		7		8		9		10			
A	Type of circuit	Electrical Features P (kW) I (A)		Wire Destination From To		Sheet N°	Designation	Color	Section	Wire Type	Câble end										
											From		To								
B	POWER CIRCUIT	4 kW	8.1 A	XP1.1	Q1.1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED LONG SIZE		CABLE END INSULATED								
				XP1.2	Q1.3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED LONG SIZE		CABLE END INSULATED								
				XP1.3	Q1.5	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED LONG SIZE		CABLE END INSULATED								
				KM1.2	A1.L1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				KM1.4	A1.L2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				KM1.6	A1.L3	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	2.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				A1.M	MM1	003	UNIPOLAR INSULATED ELECTRIC CABLE	G/Y	10 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
C	CONTROL CIRCUIT			XAUX1.1	KM1.A1	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				XAUX1.2	KM1.A2	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				KM1.A1	Q1.43	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				Q1.44	KM1.13	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				KM1.14	A1.FLC	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				XAUX1.3	A1.FLA	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				XAUX1.4	A1.F	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
D				XAUX1.5	A1.R	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				XAUX1.6	A1.RES	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
				XAUX1.7	A1.P24	003	UNIPOLAR INSULATED ELECTRIC CABLE	BLACK	1.5 mm²	H07V-K	CABLE END INSULATED		CABLE END INSULATED								
00		10/01/2017	Edition originale																		
Ind.	Date	Modification	Archiv.	Ind.	Date	Modification	Archiv.	WIRE LIST V212U40 VARIABLE SPEED DRIVE V212HU40 POWER 4 KW				CELLEAN OFFER		Schneider Electric		PHA1777503		Projet - No commande Project - Order No.		Indice Rev 00	Folio Sheet 005
Elec_tec_Schneider																					

A	1		2		3		4		5		6		7		8		9		10	
	TAG		SHEET		DESCRIPTION						MANUFACTURER			MANUFACTURER REF.			QTY			
	A1		003		ATV212 4KW 480V 3PH EMC IP21						SCHNEIDER ELECTRIC			ATV212HU40N4			1			
	KM1		003		CONT 9A 24VDC						SCHNEIDER ELECTRIC			LC1D09BD			1			
	Q1		003		DOL COMBINATION STARTER - TESYS GV2-DM - 2.5...4 A - 24 V DC						SCHNEIDER ELECTRIC			GV2AF3			1			
	Q1		003		MOTOR CIRCUIT BREAKER						SCHNEIDER ELECTRIC			GV2P14			1			
	Q1		003		SIDE INST AUX CONTACTS NO + NC						SCHNEIDER ELECTRIC			GVAN11			1			
	XAUX1		003		MOVING CONNECTOR SINGLE 8P 12A						SCHNEIDER ELECTRIC			LGYDC8APM			1			
	XP1		003		MOVING CONNECTOR 3P 32A IP2X						SCHNEIDER ELECTRIC			LGYDC3P32M2S			1			
					DRIVE PLATE ATV320 2.2-4 kW & ATV212 3-5.5 kW						SCHNEIDER ELECTRIC			NSYME0303CA			1			
B					DIN RAIL, WIDTH: 35mm, HEIGHT: 15mm, LENGTH: 138mm						-----			DIN RAIL T1.38			1			
					SHUTTER AND CABLE GLAND						SCHNEIDER ELECTRIC			NSYMEWGL			2			
C																				
D																				