

Note:

Drawings Not To Scale
Drawings Subject to Change Without Notice
Dimensions are inches next to [Millimeters]

Part No.:

## XVBC33

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

## Specification:

**Technical Information:** 

UL File: CSA File: CE Marked: RoHS compliant: NEMA / IP Rating: E164353 CCN NKCR LR44087 Class 3211-03

Yes

Yes NEMA 4X/12 - IP65

Description: Size:

70mm diameter

Housing Color:
Lens Color:
Bulb Color:
Supply Voltage:
Signaling Effect:
Mounting Type:
Terminal Type:
Cable Length: Black Green not applicable 250 VAC max Steady Light (10W max bulb) Integrated Locking Ring Screw Clamp

Comments:

must order bulb separately