





SECTION A-A



Creepage Distance 13mm  
 Clearance 13mm  
 Expansion (A) Max. 12mm  
 Mounting Details  
 (For M12 mounting stud)  
 Torque - 10 Nm  
 Tooth Washer M12  
 Hex Nut M12  
 Terminal screw M5  
 Terminal Assembly T = 33mm



	Scale: 0.500	Tolerancing Standard : ISO 8015 NFE02-352(n)	Units of measure : millimeter
<b>Schneider Electric</b>	<b>CLAMPTITE - CAN 75X203</b>		
	CLAMPTITE - CAN 75X203		
	Number: <b>HRB8564900</b>	Revision: <b>01</b>	Sheet: <b>1/1</b>
<small>The information is highly confidential and is the exclusive property of Schneider Electric. Copyright reserved. This drawing must not be used for any purpose other than that expressly permitted in writing by the owners and must not be disclosed or reproduced in any way without permission from the owners in writing. This drawing must be retained to the owners when the purpose has ceased.</small>		State: <b>Released for Manufacturing</b> Printed on 2017/09/29	