



WiserAir
The smart thermostat, made Wiser.

My Wiser

Designed to seamlessly fit your life with Simple Schedules and Ready Modes.

Sleek, Intuitive Design

The familiar, and informative, touch screen display makes interaction simple while Wiser Pulse emits a soft glow that indicates how the system is running.

Built in #1 Ranked Weather Service

With Wiser Forecast, Wiser Air adapts to what's happening outside using the #1 ranked weather service from Schneider Electric.

Eco IQ

Enable EcoIQ to let Wiser maximize the efficiency of the system based on the specific home and lifestyle; without sacrificing comfort.


* Features available in select areas.

Innovative Features

Wiser Air is packed with technology that drives friendly and unique features such as Comfort Boost to bring maximum comfort through just the touch of a button.

Auto Updates

Peace of mind, all the time. Wiser Air stays up-to-date through automatic updates that provide additional features and enhancements.




Make the Wiser choice.

Wiser Air is a complete home energy management solution that gives homeowners peace of mind through effortless control of comfort and savings.

Make the most of your energy™

Schneider
Electric™

Wiser Air provides streamlined remote access across all major platforms.
Be in control from anywhere at anytime.



Works with most common systems

- Forced air, radiant, heat pump (including geothermal), oil, gas and electric
- Up to 3 stages of heating
- Up to 2 stages of cooling

Wiser Air Specifications

Unit Dimensions	4in (10.2cm) H 4in (10.2cm) W 1.2in (3cm) D	Wire Gauge	18 to 22 AWG (0.33 to 0.82mm ²)
Trim Plate Dimensions	4.8in (12.2cm) H 6.3in (16cm) W 0.1in (0.3cm) D	Temperature	Resolution: 1°F (0.5°C) Control Accuracy: 1°F (0.5°C) Cooling Setpoint Range: 48°F to 95°F (9°C to 35°C) Heating Setpoint Range: 45.5°F to 92°F (7.5°C to 33°C) Display Range: 40°F to 95°F (5°C to 35°C) Remote Sensor Compatibility: 10k NTC, Type 2
Shipping Weight	1.32lb (599g)	Humidity Sensor	Manufacturer Calibrated: not required Precision: RH +/-3% Dehumidification range: N/A
Screen	5.4cm (2.1in) H 7.2cm (2.8in) W 640 x 480 RGB	Light Sensor	Application: LCD - Auto dim
Power Requirements	Input: ~24Vac (+/-15%), 50/60Hz Consumption: 6VA Maximum rating: 100VA, 4.17A Class 2 circuits only	Occupancy Sensor	Application: LCD wake-up Wiser Pulse intensity
Output Ratings	Maximum output: 94VA Relay rating: ~24Vac, 50/60Hz, 1A In-rush = 3A Connections: G, W, W2, Y, Y2, U, O/B Class 2 circuits only	Safety Standards	UL 873 CSA C22.2 No. 24-93
Operating Conditions	Temperature: 32°F to 104°F (0°C to 40°C) Humidity: 0% to 75% R.H. non-condensing	EMC and Radio Standards	EMC: FCC 15 Subpart B ICES-003 Radio: FCC 15 Subpart C RSS 210
Storage Conditions	Temperature: -22°F to 122°F (-30°C to 50°C) Humidity: 0% to 75% R.H. non-condensing Indoor, Dry, Pollution Degree 2	Network	ZigBee (on-board) Wi-Fi (802.11 b/g/n, 2.4GHz) Open ADR ready

Ordering Information

- **CANADA:** WISERAIR10BLKCA and WISERAIR10WHTCA
- **USA:** WISERAIR10BLKUS and WISERAIR10WHTUS



wiserhome.com

e-mail: wiser_info@schneider-electric.com
call: 1-855-55WISER (1-855-559-4737)

Schneider Electric USA

1415 S. Roselle Road
Palatine, IL 60067
Tel: 1-855-559-4737
Fax: 847-925-7500

www.schneider-electric.com/us