



A beautiful face that endears and endures

With its ultra-clean lines, sleekly chic square profile and instantly identifiable round dolly, ULTI blends two contrasting geometries to create modern simplicity of unprecedented freshness.

The design overcomes the clutter of a large central mechanism or the redundant lines of a surround frame. It results in maximum scope to showcase the synergy of color, material and finish in a standard-sized wall plate.

Adding the final touch, ring-shaped LED locators glow pleasingly to guide you to your switches at night.





Smarthouse Best Buy Award (2004)





Award (2005)



Custom Retailer EXCITE Award (2008)



TechHome Mark of Excellence (2008)



United Kingdom (2004)



Top 50 desirable designs for the home, HK (2004)



Best Custom Installation Product of The Year (2005)



Electronic House Product of the Year Award (2008)



Innovative Housing Technology Awards (2008)

The art of impression

ULTI is for those who seek the haute couture in space design. Marrying the highest aesthetics in cosmopolitan décor and superb functionality in the art of fine lighting, the award-winning ULTI range delights your vision with pure pleasure, and lights up your senses with splendour... bringing you to another level of inspired living.


Features and benefits

- Award winning design
- Clear square profile for a modern & chic appearance
- · Instantly identifiable round dolly
- · Soft radiant blue backlight for switches
- Hotel & Home Automation solutions available in the same finishes
- Maximized space of the face plate
- Ionized metal grid gives strength and stability
- Mechanical switch with touch and feel of electronic switch with patented impress mechanism



iso-motion-press mechanism

ULTI's unique iso-motion-press (i.m.press) mechanism ensures switches stay in a uniform position and can be swiftly and surely operated with a simple motion. With dollies maintaining the same position whether on or off, i.m.press empowers the world's first ever fully flush-faced 250V-rated mechanical switch.



A wealth of creative possibilities

See your imagination come to life with our crystal glass, champagne gold, brushed silver and pearl white finishes.









Range

Gang 250V 16AX, 1 Way Switch module, Blue LED Module Gang 250V 16AX, 2 Way Switch module, Blue LED Module Brushed Silver Champagne Gold Crystal Glass	U201SPM/1>B00-OS U201SPM/2>B00-OS
UC21SW/P>XBS-O! Gang Push-Push Switch Cover Plate Brushed Silver Champagne Gold Crystal Glass	U201SPM/2>B00-OS
UC21SW/P>XBS-O: Gang Push-Push Switch Cover Plate Champagne Gold Crystal Glass	
Gang Push-Push Switch Cover Plate Crystal Glass	UC21SW/P>XBS-OS
Crystal Glass	UC21SW/P>XCG-OS
De al Mille	UC21SW/P>XGL-OS
UC21SW/P>XGL-0 Pearl White	UC21SW/P>XPW-OS
2 Gang 250V 16AX, 1 Way Switch module, Blue LED Module	U202SPM/1>B00-OS
2 Gang 250V 16AX, 2 Way Switch module, Blue LED Module	U202SPM/2>B00-OS
UC22SW/P>XBS-OS UC22SW/P>XCG-OS Brushed Silver	UC22SW/P>XBS-OS
Champagne Gold	UC22SW/P>XCG-OS
2 Gang Push-Push Switch Cover Plate Crystal Glass	UC22SW/P>XGL-OS
uczzsw/P>xgl-os uczzsw/P>xpw-os Pearl White	UC22SW/P>XPW-OS
4 Gang 250V 16AX, 1 Way Switch module Blue LED Module	U204SPM/1>B00-OS
4 Gang 250V 16AX, 2 Way Switch module Blue LED Module	U204SPM/2>B00-OS
UC24SW/P>XBS-OS UC24SW/P>XCG-OS Brushed Silver	UC24SW/P>XBS-OS
Champagne Gold	UC24SW/P>XCG-OS
4 Gang Push-Push Switch Cover Plate Crystal Glass	UC24SW/P>XGL-OS
uc24sw/p>xgl-os uc24sw/p>xpw-os Pearl White	UC24SW/P>XPW-OS
Bell Press Switch, Module with Blue LED Module	US31BPB00
Brushed Silver	UC31BPXBS
UC31BPXGS UC31BPXCG Champagne Gold	UC31BPXCG
Bell Press Switch, Cover Plate Crystal Glass	UC31BPXGL
UC31BPXGL UC31BPXPW Pearl White	UC31BPXPW
1 Gang 250V 20A Double Pole Switch module, Blue LED Module	U201SPM/DP>B00-OS
Brushed Silver	UC21DP/P>XBS-OS
UC21DP/P>XBS-OS UC21DP/P>XCG-OS Champagne Gold	UC21DP/P>XCG-OS
1 Gang Push-Push, DP Switch, Cover Plate Crystal Glass	UC21DP/P>XGL-OS
UC21DP/P>XGL-OS UC21DP/P>XPW-OS	UC21DP/P>XPW-OS
6-16A Switched Socket Module	US15/616000
Brushed Silver	UC15/616XBS
UC15/616XBS UC15/616XCG Champagne Gold	UC15/616XCG
6-16A Switched Socket, Cover Plate Crystal Glass	UC15/616XGL
Pearl White	UC15/616XPW
6A 2/3 Pin Switched Socket Module	US15/6U000
Brushed Silver	UC15/6UXBS
UC15/6UXBS UC15/6UXCG Champagne Gold	UC15/6UXCG
6A 2/3 Pin Switched Socket, Cover Plate Crystal Glass	UC15/6UXGL
UC15/6UXGL UC15/6UXPW	UC15/6UXPW
International Socket Module	US426/16IS000
Brushed Silver	UC426/16ISXBS
UC426/16ISXBS UC426/16ISXCG Champagne Gold	UC426/16ISXCG
International Socket Cover Plate Crystal Glass	UC426/16ISXGL
	UC426/16ISXPW

Range

		Description	Colour	Reference
		Blank Module	Module	US31X000
		Blank Module, Cover Plate	Brushed Silver	UC31XXBS
UC31XXBS			Champagne Gold	UC31XXCG
			Crystal Glass	UC31XXGL
UC31XXGL			Pearl White	UC31XXPW
		TV Socket Module	Module	US31TV000
UC31TVXBS		TV Socket, Cover Plate	Brushed Silver	UC31TVXBS
			Champagne Gold	UC31TVXCG
1			Crystal Glass	UC31TVXGL
UC31TVXGL			Pearl White	UC31TVXPW
	1	Data Socket Module	Module	UD31RJ000
	UDC31RJXCG	Data Socket, Cover Plate	Brushed Silver	UDC31RJXBS
UDC31RJXBS			Champagne Gold	UDC31RJXCG
(2)			Crystal Glass	UDC31RJXGL
UDC31RJXGL	UDC31RJXPW		Pearl White	UDC31RJXPW
		Twin Data Socket Module	Module	UD32TD000
	UDC32TDXCG	Twin Data Socket, Cover Plate	Brushed Silver	UDC32TDXBS
UDC32TDXBS			Champagne Gold	UDC32TDXCG
			Crystal Glass	UDC32TDXGL
UDC32TDXGL	UDC32TDXPW		Pearl White	UDC32TDXPW
13 8	UC31USB_XCG	1 Gang 2.1A, USB Charger Module, White 1 Gang 2.1A, USB Charger Cover Plate	White	US31USB_WE
œ.			Grey	US31USB_GY
UC31USB_XBS			Brushed Silver	UC31USB_XBS
1	1		Champagne Gold	UC31USB_XCG
0	(0)		Crystal Glass	UC31USB_XGL
UC31USB_XGL	UC31USB_XPW		Pearl White	UC31USB_XPW
		Keycard Switch	Brushed Silver	U31EKTHBBS
U31EKTHACG	U31EKTHBBS		Champagne Gold	U31EKTHACG
			Crystal Glass	U31EKTHBGL
U31EKTHBGL	U31EKTHBPW		Pearl White	U31EKTHBPW
15 (12)	E (1)	Shaver Socket	Brushed Silver	US727HXBS
US727HXBS	US727HXCG		Champagne Gold	US727HXCG
<u> </u>	E (1)		Crystal Glass	US727HXGL
US727HXGL	US727HXPW		Pearl White	US727HXPW
		Metal Boxes for BS Format Ranges (ULTI, NEO, ZENcelo BS)		
1 mm thickness				
2 Gang GI Metal Boxes to accommodate up to 2 Units			GM1102	
3 Gang GI Metal Boxes to accommodate up to 3 Units			GM1103	
	4 Gang GI Metal Boxes to accommodate up to 4 Units			GM1104