

**Applications**

General protection and protection of motors fitted with PTC thermistor probes <sup>(1)</sup>



**Standards and approvals**

IEC 60034-11, UL, CSA

**Reset method**

Automatic

**Fault signalling**

–

**Fault memory in the event of a supply failure**

–

**Fault test**

–

**Rated control circuit voltages  
~ 50/60 Hz**

Single voltage 115 V or 230 V

**Rated control circuit voltages ---**

Single voltage 24 V

**Contact type**

1 N/C

**Protection unit type**

**LT3 SE**

**Pages**

27065/2

<sup>(1)</sup> PTC: Positive Temperature Coefficient



IEC 60034-11, PTB, UL, CSA  
LROS

Automatic

Manual or automatic

On front panel of unit and remote

–

Yes

–

By pushbutton on front panel of unit

Dual voltage 115/230 V  
Multivoltage 24...230 V

Single voltage 400 V  
Dual voltage 24/48 V, 115/230 V  
Multivoltage 24...230 V

Dual voltage 24/48 V

Dual voltage 24/48 V  
Multivoltage 24...230 V

Dual voltage 1 N/C + 1 N/O  
Multivoltage 2 C/O

Single voltage or dual voltage 1 N/C + 1 N/O  
Multivoltage 2 C/O

**LT3 SA**

**LT3 SM**

27065/2