

Surface mounting Mini Pragma (offer B)

1 row, 4 to 18 modules

2 and 3 rows, 12 modules per row



Connection assembly



13379



13922

Function

Mini Pragma is a distribution or subdistribution enclosure up to 63 A. It is used indoors, in housing or the service sector, for new installations or renovation work.

Description

Technical data

- Equipped with an opaque or transparent, curved door:
 - 1 row: wicket door opens 90° upwards
 - 2 and 3 rows: door opens 180° to the right and to the left.
- Rated current of the enclosure:
 - 4 modules: 50 A
 - 6 to 36 modules: 63 A.
- Material:
 - colour: white RAL 9003.
- Compliance with standards:
 - complies with IEC 439.3 (EN 60-439-3).
- Degree of protection:
 - as in IEC 529: IP40 (protection against solids and liquids)
 - as in EN 50-102: IK07 (protection against mechanical impacts)
 - class 2 protection against indirect contact (with insulating plugs on the fixing screws).
- Fire and excessive heat withstand capacity: as in IEC 695-2-1:
 - enclosure: 650°C/30 s
 - N - earth terminal bar supports: 960°C/30 s.

Composition

Surface mounting Mini Pragma is composed of:

- a back with:
 - a centred oblong opening to simplify installation
 - oblong fixing holes enabling the adjustment of verticality
- cable insertion kit:
 - punch-outs, on 4 panels for the 1 row enclosures
 - a large surface for punching (crown saw, punches) at the top and bottom of the 2 and 3 row enclosures
- 1 to 3 metallic rails, screwed symmetrically onto the back
- a cover:
 - reversible front panel, equipped with blanking plates which can be punched-out
 - curved wicket door or curved door.

Accessories delivered with the enclosure

Surface mounting Mini Pragma is delivered equipped with:

- insulating plugs:
 - to be placed on the back fixing screws to obtain a class 2 insulation
- a circuit identification strip per row:
 - to be glued onto the front panel
- a connection assembly:
 - 2 earth-neutral terminal blocks
 - 2 terminal block supports
- terminal block details:

Number of holes	Composition	
	10 [□]	16 [□]
4	2	2
8	4	4
16	8	8
22	11	11
32	16	16

Surface mounting Mini Pragma (offer B)

1 row, 4 to 18 modules

2 and 3 rows, 12 modules per row (cont.)

Catalogue numbers

Enclosure with door					
Number of rows	Capacity in modules		Terminal blocks delivered (no. x no. holes)	Cat. no.	
	of 9 mm	of 18 mm		Opaque	Transparent
1	8	4	2 x 4	13376	13366
1	12	6	2 x 4	13377	13367
1	16	8	2 x 8	13378	13368
1	24	12	(2 x 4) + (2 x 8)	13379	13369
1	36	18	2 x 16	13380	13370
2	48	24	2 x 16	13912	13922
3	72	36	2 x 22	13913	13923

Additional information

Optional accessories: page 93010

Dimensions: page 93900